


MODEL	ACCESS LETTER	DIMENSIONS (IN)				VOLUME (GAL)		WEIGHT (LBS)*		UNIT	
		A	B	C	D	MAX	MIN	SHIP	OPER.	JC	JW
RS 55	B, C	34	84	40 1/2	40	155	85	420	1,715	25 - 58	10A - 15C
RS 150	D, E	50	84	40 1/2	40	248	178	505	2,575	63 - 120	25A - 35C
RS 250	F	56	98	55	40	393	295	665	3,940	135 - 200	50A - 50C
RS 450	G, H	70	107	66	40	614	495	805	5,920	240 - 350	70B - 85C
RS 850	I, J	70	167	124	40	1,178	952	1,330	11,145	375 - 450	100B - 115C
RS 930	K	70	178	135	40	1,286	1,038	1,405	12,120	475 - 525	130B - 130C



SCHEMATIC VIEWS ONLY
SOME DETAILS REMOVED FOR CLARITY

NOTES:

- 1) MECHANICAL WATER MAKE-UP SYSTEM FACTORY INSTALLED.
 - 2) PUMP(S) NOT INCLUDED: CONSULT RECOLD REPRESENTATIVE FOR PRICING. (PIPING HEAD LOSS INFORMATION REQUIRED)
 - 3) CONTACT RECOLD REPRESENTATIVE FOR JT & M-SERIES MODEL SELECTION.
- * WEIGHTS DO NOT INCLUDE PUMP(S) OR OTHER OPTIONS.

REMOTE SUMP			
	SCALE	DRAWN DATE:	DRAWN BY:
	NONE		BRK
PART NO.:		DATE REVISED:	
FORM 8100		REV A	