







MD5030WAKM	1958	75	30.0	30.0	33.4
MD5030WAKN	1918	75	30.0	34.5	33.4
MD5030WALK	1949	75	30.0	30.0	31.4
MD5030WALL	1914	75	30.0	34.5	31.4
MD5030WALM	1996	75	30.0	30.0	34.4
MD5030WALN	1958	75	30.0	34.5	34.4
MD5030WAMK	1964	75	30.0	30.0	32.4
MD5030WAML	1930	75	30.0	34.5	32.4
MD5030WAMM	2008	75	30.0	30.0	35.4
MD5030WAMN	1973	75	30.0	34.5	35.4
MD5030WAUK	1772	75	30.0	30.0	30.4
MD5030WAUL	1725	75	30.0	34.5	30.4
MD5030WAUM	1831	75	30.0	30.0	33.4
MD5030WAUN	1779	75	30.0	34.5	33.4
MD5030WAVK	1899	75	30.0	30.0	32.4
MD5030WAVL	1853	75	30.0	34.5	32.4
MD5030WAVM	1957	75	30.0	30.0	35.4
MD5030WAVN	1907	75	30.0	34.5	35.4
MD5030WAWK	1950	75	30.0	30.0	32.4
MD5030WAWL	1905	75	30.0	34.5	32.4
MD5030WAWM	2008	75	30.0	30.0	35.4
MD5030WAWN	1959	75	30.0	34.5	35.4
MD5030WBHK	1986	75	30.0	30.0	30.4
MD5030WBHL	1952	75	30.0	34.5	30.4
MD5030WBHM	2081	75	30.0	30.0	33.4
MD5030WBHN	2042	75	30.0	34.5	33.4
MD5030WBJK	2026	75	30.0	30.0	31.4
MD5030WBJL	1995	75	30.0	34.5	31.4
MD5030WBJM	2116	75	30.0	30.0	34.4
MD5030WBJN	2080	75	30.0	34.5	34.4
MD5030WBKK	1885	75	30.0	30.0	30.4
MD5030WBKL	1852	75	30.0	34.5	30.4
MD5030WBKM	1979	75	30.0	30.0	33.4
MD5030WBKN	1940	75	30.0	34.5	33.4
MD5030WBLK	1931	75	30.0	30.0	31.4
MD5030WBLL	1899	75	30.0	34.5	31.4
MD5030WBLM	2020	75	30.0	30.0	34.4
MD5030WBLN	1983	75	30.0	34.5	34.4
MD5030WBMK	1952	75	30.0	30.0	32.4
MD5030WBML	1923	75	30.0	34.5	32.4
MD5030WBMM	2036	75	30.0	30.0	35.4
MD5030WBMN	2002	75	30.0	34.5	35.4
MD5030WBUK	1730	75	30.0	30.0	30.4
MD5030WBUL	1688	75	30.0	34.5	30.4
MD5030WBUM	1845	75	30.0	30.0	33.4
MD5030WBUN	1794	75	30.0	34.5	33.4
MD5030WBVK	1860	75	30.0	30.0	32.4
MD5030WBVL	1820	75	30.0	34.5	32.4
MD5030WBVM	1975	75	30.0	30.0	35.4
MD5030WBVN	1926	75	30.0	34.5	35.4
MD5030WBWK	1914	75	30.0	30.0	32.4
MD5030WBWL	1874	75	30.0	34.5	32.4
MD5030WBWM	2027	75	30.0	30.0	35.4
MD5030WBWN	1979	75	30.0	34.5	35.4
MD5030WDHK	1992	75	30.0	30.0	30.4
MD5030WDHL	1957	75	30.0	34.5	30.4
MD5030WDHM	2086	75	30.0	30.0	33.4
MD5030WDHN	2045	75	30.0	34.5	33.4
MD5030WDJK	2031	75	30.0	30.0	31.4
MD5030WDJL	1998	75	30.0	34.5	31.4
MD5030WDJM	2119	75	30.0	30.0	34.4
MD5030WDJN	2081	75	30.0	34.5	34.4
MD5030WDKK	1894	75	30.0	30.0	30.4
MD5030WDKL	1859	75	30.0	34.5	30.4
MD5030WDKM	1986	75	30.0	30.0	33.4
MD5030WDKN	1946	75	30.0	34.5	33.4
MD5030WDLK	1938	75	30.0	30.0	31.4
MD5030WDLL	1905	75	30.0	34.5	31.4
MD5030WDLM	2025	75	30.0	30.0	34.4
MD5030WDLN	1987	75	30.0	34.5	34.4
MD5030WDMK	1957	75	30.0	30.0	32.4
MD5030WDMML	1926	75	30.0	34.5	32.4
MD5030WDMMM	2039	75	30.0	30.0	35.4
MD5030WDMN	2003	75	30.0	34.5	35.4
MD5030WDUK	1744	75	30.0	30.0	30.4
MD5030WDUL	1700	75	30.0	34.5	30.4
MD5030WDUM	1858	75	30.0	30.0	33.4
MD5030WDUN	1805	75	30.0	34.5	33.4
MD5030WDVK	1874	75	30.0	30.0	32.4
MD5030WDVL	1832	75	30.0	34.5	32.4
MD5030WDVM	1986	75	30.0	30.0	35.4
MD5030WDVN	1936	75	30.0	34.5	35.4
MD5030WDWK	1926	75	30.0	30.0	32.4
MD5030WDWL	1885	75	30.0	34.5	32.4
MD5030WDWM	2037	75	30.0	30.0	35.4
MD5030WDWN	1989	75	30.0	34.5	35.4
MD5030WLHK	1989	75	30.0	30.0	30.4
MD5030WLHL	1950	75	30.0	34.5	30.4
MD5030WLHM	2040	75	30.0	30.0	33.4
MD5030WLHN	1999	75	30.0	34.5	33.4

MD5030WLJK	2020	75	30.0	30.0	31.4
MD5030WLJL	1984	75	30.0	34.5	31.4
MD5030WLJM	2069	75	30.0	30.0	34.4
MD5030WLJN	2031	75	30.0	34.5	34.4
MD5030WLKK	1899	75	30.0	30.0	30.4
MD5030WLKL	1860	75	30.0	34.5	30.4
MD5030WLKM	1948	75	30.0	30.0	33.4
MD5030WLKN	1907	75	30.0	34.5	33.4
MD5030WLLK	1936	75	30.0	30.0	31.4
MD5030WLLL	1900	75	30.0	34.5	31.4
MD5030WLLM	1984	75	30.0	30.0	34.4
MD5030WLLN	1945	75	30.0	34.5	34.4
MD5030WLMK	1947	75	30.0	30.0	32.4
MD5030WLML	1913	75	30.0	34.5	32.4
MD5030WLMM	1993	75	30.0	30.0	35.4
MD5030WLMN	1957	75	30.0	34.5	35.4
MD5030WLUK	1766	75	30.0	30.0	30.4
MD5030WLUL	1718	75	30.0	34.5	30.4
MD5030WLUM	1826	75	30.0	30.0	33.4
MD5030WLUN	1773	75	30.0	34.5	33.4
MD5030WLVK	1891	75	30.0	30.0	32.4
MD5030WLVL	1844	75	30.0	34.5	32.4
MD5030WLVM	1950	75	30.0	30.0	35.4
MD5030WLVN	1899	75	30.0	34.5	35.4
MD5030WLWK	1941	75	30.0	30.0	32.4
MD5030WLWL	1895	75	30.0	34.5	32.4
MD5030WLWM	2000	75	30.0	30.0	35.4
MD5030WLWN	1950	75	30.0	34.5	35.4
MD5030XAHK	2198	100	30.0	30.0	30.4
MD5030XAHL	2157	100	30.0	34.5	30.4
MD5030XAHM	2252	100	30.0	30.0	33.4
MD5030XAHN	2209	100	30.0	34.5	33.4
MD5030XAJK	2237	100	30.0	30.0	31.4
MD5030XAJL	2199	100	30.0	34.5	31.4
MD5030XAJM	2289	100	30.0	30.0	34.4
MD5030XAJN	2248	100	30.0	34.5	34.4
MD5030XAKK	2080	100	30.0	30.0	30.4
MD5030XAKL	2040	100	30.0	34.5	30.4
MD5030XAKM	2130	100	30.0	30.0	33.4
MD5030XAKN	2088	100	30.0	34.5	33.4
MD5030XALK	2125	100	30.0	30.0	31.4
MD5030XALL	2088	100	30.0	34.5	31.4
MD5030XALM	2173	100	30.0	30.0	34.4
MD5030XALN	2134	100	30.0	34.5	34.4
MD5030XAMK	2145	100	30.0	30.0	32.4
MD5030XAML	2110	100	30.0	34.5	32.4
MD5030XAMM	2191	100	30.0	30.0	35.4
MD5030XAMN	2154	100	30.0	34.5	35.4
MD5030XAUK	1948	100	30.0	30.0	30.4
MD5030XAUL	1895	100	30.0	34.5	30.4
MD5030XAUM	2013	100	30.0	30.0	33.4
MD5030XAUN	1955	100	30.0	34.5	33.4
MD5030XAVK	2084	100	30.0	30.0	32.4
MD5030XAVL	2033	100	30.0	34.5	32.4
MD5030XAVM	2148	100	30.0	30.0	35.4
MD5030XAVN	2093	100	30.0	34.5	35.4
MD5030XAWK	2139	100	30.0	30.0	32.4
MD5030XAWL	2090	100	30.0	34.5	32.4
MD5030XAWM	2203	100	30.0	30.0	35.4
MD5030XAWN	2150	100	30.0	34.5	35.4
MD5030XBHK	2186	100	30.0	30.0	30.4
MD5030XBHL	2148	100	30.0	34.5	30.4
MD5030XBHM	2286	100	30.0	30.0	33.4
MD5030XBHN	2241	100	30.0	34.5	33.4
MD5030XBJK	2229	100	30.0	30.0	31.4
MD5030XBJL	2193	100	30.0	34.5	31.4
MD5030XBJM	2323	100	30.0	30.0	34.4
MD5030XBJN	2282	100	30.0	34.5	34.4
MD5030XBKK	2064	100	30.0	30.0	30.4
MD5030XBKL	2027	100	30.0	34.5	30.4
MD5030XBKM	2157	100	30.0	30.0	33.4
MD5030XBKN	2116	100	30.0	34.5	33.4
MD5030XBLK	2113	100	30.0	30.0	31.4
MD5030XBLL	2078	100	30.0	34.5	31.4
MD5030XBLM	2202	100	30.0	30.0	34.4
MD5030XBLN	2162	100	30.0	34.5	34.4
MD5030XBMK	2137	100	30.0	30.0	32.4
MD5030XBML	2104	100	30.0	34.5	32.4
MD5030XBMM	2221	100	30.0	30.0	35.4
MD5030XBMN	2184	100	30.0	34.5	35.4
MD5030XBUK	1918	100	30.0	30.0	30.4
MD5030XBUL	1869	100	30.0	34.5	30.4
MD5030XBUM	2042	100	30.0	30.0	33.4
MD5030XBUN	1984	100	30.0	34.5	33.4
MD5030XBVK	2057	100	30.0	30.0	32.4
MD5030XBVL	2011	100	30.0	34.5	32.4
MD5030XBVM	2179	100	30.0	30.0	35.4
MD5030XBVN	2124	100	30.0	34.5	35.4
MD5030XBWK	2115	100	30.0	30.0	32.4
MD5030XBWL	2069	100	30.0	34.5	32.4

MD5030XBWM	2235	100	30.0	30.0	35.4
MD5030XBWN	2181	100	30.0	34.5	35.4
MD5030XDHK	2178	100	30.0	30.0	30.4
MD5030XDHL	2139	100	30.0	34.5	30.4
MD5030XDHM	2275	100	30.0	30.0	33.4
MD5030XDHN	2231	100	30.0	34.5	33.4
MD5030XDJK	2219	100	30.0	30.0	31.4
MD5030XDJL	2183	100	30.0	34.5	31.4
MD5030XDJM	2311	100	30.0	30.0	34.4
MD5030XDJN	2269	100	30.0	34.5	34.4
MD5030XDKK	2060	100	30.0	30.0	30.4
MD5030XDKL	2022	100	30.0	34.5	30.4
MD5030XDKM	2150	100	30.0	30.0	33.4
MD5030XDKN	2108	100	30.0	34.5	33.4
MD5030XDLK	2107	100	30.0	30.0	31.4
MD5030XDLL	2071	100	30.0	34.5	31.4
MD5030XDLM	2193	100	30.0	30.0	34.4
MD5030XDLN	2153	100	30.0	34.5	34.4
MD5030XDMK	2129	100	30.0	30.0	32.4
MD5030XDML	2095	100	30.0	34.5	32.4
MD5030XDMM	2211	100	30.0	30.0	35.4
MD5030XDMN	2173	100	30.0	34.5	35.4
MD5030XDUK	1917	100	30.0	30.0	30.4
MD5030XDUL	1867	100	30.0	34.5	30.4
MD5030XDUM	2038	100	30.0	30.0	33.4
MD5030XDUN	1979	100	30.0	34.5	33.4
MD5030XDVK	2055	100	30.0	30.0	32.4
MD5030XDVL	2008	100	30.0	34.5	32.4
MD5030XDVM	2174	100	30.0	30.0	35.4
MD5030XDVN	2118	100	30.0	34.5	35.4
MD5030XDWK	2112	100	30.0	30.0	32.4
MD5030XDWL	2065	100	30.0	34.5	32.4
MD5030XDWM	2229	100	30.0	30.0	35.4
MD5030XDWN	2174	100	30.0	34.5	35.4
MD5030XLHK	2185	100	30.0	30.0	30.4
MD5030XLHL	2144	100	30.0	34.5	30.4
MD5030XLHM	2240	100	30.0	30.0	33.4
MD5030XLHN	2196	100	30.0	34.5	33.4
MD5030XLJK	2222	100	30.0	30.0	31.4
MD5030XLJL	2183	100	30.0	34.5	31.4
MD5030XLJM	2275	100	30.0	30.0	34.4
MD5030XLJN	2233	100	30.0	34.5	34.4
MD5030XLKK	2070	100	30.0	30.0	30.4
MD5030XLKL	2030	100	30.0	34.5	30.4
MD5030XLKM	2120	100	30.0	30.0	33.4
MD5030XLKN	2078	100	30.0	34.5	33.4
MD5030XLLK	2114	100	30.0	30.0	31.4
MD5030XLLL	2076	100	30.0	34.5	31.4
MD5030XLLM	2162	100	30.0	30.0	34.4
MD5030XLLN	2123	100	30.0	34.5	34.4
MD5030XLMK	2132	100	30.0	30.0	32.4
MD5030XLML	2096	100	30.0	34.5	32.4
MD5030XLMM	2179	100	30.0	30.0	35.4
MD5030XLMN	2142	100	30.0	34.5	35.4
MD5030XLUK	1938	100	30.0	30.0	30.4
MD5030XLUL	1885	100	30.0	34.5	30.4
MD5030XLUM	2003	100	30.0	30.0	33.4
MD5030XLUN	1946	100	30.0	34.5	33.4
MD5030XLVK	2074	100	30.0	30.0	32.4
MD5030XLVL	2023	100	30.0	34.5	32.4
MD5030XLVM	2137	100	30.0	30.0	35.4
MD5030XLVN	2083	100	30.0	34.5	35.4
MD5030XLWK	2129	100	30.0	30.0	32.4
MD5030XLWL	2079	100	30.0	34.5	32.4
MD5030XLWM	2192	100	30.0	30.0	35.4
MD5030XLWN	2139	100	30.0	34.5	35.4
MD5030YAHK	2372	125	30.0	30.0	32.4
MD5030YAHL	2345	125	30.0	34.5	32.4
MD5030YAHM	2428	125	30.0	30.0	35.4
MD5030YAHN	2399	125	30.0	34.5	35.4
MD5030YAJK	2415	125	30.0	30.0	33.4
MD5030YAJL	2390	125	30.0	34.5	33.4
MD5030YAJM	2468	125	30.0	30.0	36.4
MD5030YAJN	2442	125	30.0	34.5	36.4
MD5030YAKK	2228	125	30.0	30.0	32.4
MD5030YAKL	2202	125	30.0	34.5	32.4
MD5030YAKM	2277	125	30.0	30.0	35.4
MD5030YAKN	2250	125	30.0	34.5	35.4
MD5030YALK	2276	125	30.0	30.0	33.4
MD5030YALL	2252	125	30.0	34.5	33.4
MD5030YALM	2324	125	30.0	30.0	36.4
MD5030YALN	2299	125	30.0	34.5	36.4
MD5030YAMK	2302	125	30.0	30.0	34.4
MD5030YAML	2279	125	30.0	34.5	34.4
MD5030YAMM	2348	125	30.0	30.0	37.4
MD5030YAMN	2324	125	30.0	34.5	37.4
MD5030YAUK	2110	125	30.0	30.0	32.4
MD5030YAUL	2073	125	30.0	34.5	32.4
MD5030YAUM	2179	125	30.0	30.0	35.4
MD5030YAUN	2139	125	30.0	34.5	35.4

MD5030YAVK	2252	125	30.0	30.0	34.4
MD5030YAVL	2218	125	30.0	34.5	34.4
MD5030YAVM	2320	125	30.0	30.0	37.4
MD5030YAVN	2282	125	30.0	34.5	37.4
MD5030YAWK	2312	125	30.0	30.0	34.4
MD5030YAWL	2278	125	30.0	34.5	34.4
MD5030YAWM	2378	125	30.0	30.0	37.4
MD5030YAWN	2342	125	30.0	34.5	37.4
MD5030YBHK	2348	125	30.0	30.0	32.4
MD5030YBHL	2323	125	30.0	34.5	32.4
MD5030YBHM	2456	125	30.0	30.0	35.4
MD5030YBHN	2428	125	30.0	34.5	35.4
MD5030YBJK	2398	125	30.0	30.0	33.4
MD5030YBJL	2375	125	30.0	34.5	33.4
MD5030YBJM	2500	125	30.0	30.0	36.4
MD5030YBJN	2474	125	30.0	34.5	36.4
MD5030YBKK	2200	125	30.0	30.0	32.4
MD5030YBKL	2177	125	30.0	34.5	32.4
MD5030YBKM	2298	125	30.0	30.0	35.4
MD5030YBKN	2272	125	30.0	34.5	35.4
MD5030YBLK	2254	125	30.0	30.0	33.4
MD5030YBLL	2233	125	30.0	34.5	33.4
MD5030YBLM	2347	125	30.0	30.0	36.4
MD5030YBLN	2323	125	30.0	34.5	36.4
MD5030YBMK	2286	125	30.0	30.0	34.4
MD5030YBML	2266	125	30.0	34.5	34.4
MD5030YBMM	2374	125	30.0	30.0	37.4
MD5030YBMN	2351	125	30.0	34.5	37.4
MD5030YBUK	2060	125	30.0	30.0	32.4
MD5030YBUL	2026	125	30.0	34.5	32.4
MD5030YBUM	2199	125	30.0	30.0	35.4
MD5030YBUN	2159	125	30.0	34.5	35.4
MD5030YBVK	2207	125	30.0	30.0	34.4
MD5030YBVL	2175	125	30.0	34.5	34.4
MD5030YBVM	2342	125	30.0	30.0	37.4
MD5030YBVN	2305	125	30.0	34.5	37.4
MD5030YBWK	2268	125	30.0	30.0	34.4
MD5030YBWL	2238	125	30.0	34.5	34.4
MD5030YBWM	2403	125	30.0	30.0	37.4
MD5030YBWN	2366	125	30.0	34.5	37.4
MD5030YDHK	2351	125	30.0	30.0	32.4
MD5030YDHL	2325	125	30.0	34.5	32.4
MD5030YDHM	2455	125	30.0	30.0	35.4
MD5030YDHN	2425	125	30.0	34.5	35.4
MD5030YDJK	2395	125	30.0	30.0	33.4
MD5030YDJL	2371	125	30.0	34.5	33.4
MD5030YDJM	2493	125	30.0	30.0	36.4
MD5030YDJN	2465	125	30.0	34.5	36.4
MD5030YDKK	2208	125	30.0	30.0	32.4
MD5030YDKL	2183	125	30.0	34.5	32.4
MD5030YDKM	2301	125	30.0	30.0	35.4
MD5030YDKN	2273	125	30.0	34.5	35.4
MD5030YDLK	2258	125	30.0	30.0	33.4
MD5030YDLL	2235	125	30.0	34.5	33.4
MD5030YDLM	2346	125	30.0	30.0	36.4
MD5030YDLN	2321	125	30.0	34.5	36.4
MD5030YDMK	2285	125	30.0	30.0	34.4
MD5030YDML	2263	125	30.0	34.5	34.4
MD5030YDMM	2369	125	30.0	30.0	37.4
MD5030YDMN	2345	125	30.0	34.5	37.4
MD5030YDUK	2082	125	30.0	30.0	32.4
MD5030YDUL	2046	125	30.0	34.5	32.4
MD5030YDUM	2216	125	30.0	30.0	35.4
MD5030YDUN	2174	125	30.0	34.5	35.4
MD5030YDVK	2225	125	30.0	30.0	34.4
MD5030YDVL	2192	125	30.0	34.5	34.4
MD5030YDVM	2355	125	30.0	30.0	37.4
MD5030YDVN	2316	125	30.0	34.5	37.4
MD5030YDWK	2285	125	30.0	30.0	34.4
MD5030YDWL	2252	125	30.0	34.5	34.4
MD5030YDWM	2413	125	30.0	30.0	37.4
MD5030YDWN	2375	125	30.0	34.5	37.4
MD5030YLHK	2347	125	30.0	30.0	32.4
MD5030YLHL	2319	125	30.0	34.5	32.4
MD5030YLHM	2405	125	30.0	30.0	35.4
MD5030YLHN	2375	125	30.0	34.5	35.4
MD5030YLJK	2385	125	30.0	30.0	33.4
MD5030YLJL	2359	125	30.0	34.5	33.4
MD5030YLJM	2441	125	30.0	30.0	36.4
MD5030YLJN	2413	125	30.0	34.5	36.4
MD5030YLKK	2210	125	30.0	30.0	32.4
MD5030YLKL	2184	125	30.0	34.5	32.4
MD5030YLKM	2261	125	30.0	30.0	35.4
MD5030YLKN	2233	125	30.0	34.5	35.4
MD5030YLLK	2256	125	30.0	30.0	33.4
MD5030YLLL	2231	125	30.0	34.5	33.4
MD5030YLLM	2305	125	30.0	30.0	36.4
MD5030YLLN	2279	125	30.0	34.5	36.4
MD5030YLMK	2277	125	30.0	30.0	34.4
MD5030YMLM	2254	125	30.0	34.5	34.4

MD5030YLMM	2325	125	30.0	30.0	37.4
MD5030YLMN	2301	125	30.0	34.5	37.4
MD5030YLUK	2097	125	30.0	30.0	32.4
MD5030YLUL	2060	125	30.0	34.5	32.4
MD5030YLUM	2168	125	30.0	30.0	35.4
MD5030YLUN	2127	125	30.0	34.5	35.4
MD5030YLVK	2236	125	30.0	30.0	34.4
MD5030YLVL	2201	125	30.0	34.5	34.4
MD5030YLVN	2305	125	30.0	30.0	37.4
MD5030YLVN	2267	125	30.0	34.5	37.4
MD5030YLWK	2294	125	30.0	30.0	34.4
MD5030YLWL	2260	125	30.0	34.5	34.4
MD5030YLWM	2363	125	30.0	30.0	37.4
MD5030YLWN	2325	125	30.0	34.5	37.4
MD5030ZAHK	2518	150	30.0	30.0	32.4
MD5030ZAHL	2490	150	30.0	34.5	32.4
MD5030ZAHM	2573	150	30.0	30.0	35.4
MD5030ZAHN	2544	150	30.0	34.5	35.4
MD5030ZAJK	2568	150	30.0	30.0	33.4
MD5030ZAJL	2542	150	30.0	34.5	33.4
MD5030ZAJM	2621	150	30.0	30.0	36.4
MD5030ZAJN	2595	150	30.0	34.5	36.4
MD5030ZAKK	2343	150	30.0	30.0	32.4
MD5030ZAKL	2318	150	30.0	34.5	32.4
MD5030ZAKM	2390	150	30.0	30.0	35.4
MD5030ZAKN	2364	150	30.0	34.5	35.4
MD5030ZALK	2397	150	30.0	30.0	33.4
MD5030ZALL	2374	150	30.0	34.5	33.4
MD5030ZALM	2443	150	30.0	30.0	36.4
MD5030ZALN	2418	150	30.0	34.5	36.4
MD5030ZAMK	2430	150	30.0	30.0	34.4
MD5030ZAML	2408	150	30.0	34.5	34.4
MD5030ZAMM	2474	150	30.0	30.0	37.4
MD5030ZAMN	2451	150	30.0	34.5	37.4
MD5030ZAUK	2235	150	30.0	30.0	32.4
MD5030ZAUL	2197	150	30.0	34.5	32.4
MD5030ZAUM	2306	150	30.0	30.0	35.4
MD5030ZAUN	2265	150	30.0	34.5	35.4
MD5030ZAVK	2387	150	30.0	30.0	34.4
MD5030ZAVL	2352	150	30.0	34.5	34.4
MD5030ZAVM	2456	150	30.0	30.0	37.4
MD5030ZAVN	2418	150	30.0	34.5	37.4
MD5030ZAWK	2451	150	30.0	30.0	34.4
MD5030ZAWL	2417	150	30.0	34.5	34.4
MD5030ZAWM	2520	150	30.0	30.0	37.4
MD5030ZAWN	2482	150	30.0	34.5	37.4
MD5030ZBHK	2496	150	30.0	30.0	32.4
MD5030ZBHL	2470	150	30.0	34.5	32.4
MD5030ZBHM	2608	150	30.0	30.0	35.4
MD5030ZBHN	2578	150	30.0	34.5	35.4
MD5030ZBJK	2548	150	30.0	30.0	33.4
MD5030ZBJL	2523	150	30.0	34.5	33.4
MD5030ZBJM	2653	150	30.0	30.0	36.4
MD5030ZBJN	2625	150	30.0	34.5	36.4
MD5030ZBKK	2324	150	30.0	30.0	32.4
MD5030ZBKL	2300	150	30.0	34.5	32.4
MD5030ZBKM	2419	150	30.0	30.0	35.4
MD5030ZBKN	2393	150	30.0	34.5	35.4
MD5030ZBLK	2380	150	30.0	30.0	33.4
MD5030ZBLL	2357	150	30.0	34.5	33.4
MD5030ZBLM	2470	150	30.0	30.0	36.4
MD5030ZBLN	2445	150	30.0	34.5	36.4
MD5030ZBMK	2414	150	30.0	30.0	34.4
MD5030ZBML	2392	150	30.0	34.5	34.4
MD5030ZBMM	2500	150	30.0	30.0	37.4
MD5030ZBMN	2476	150	30.0	34.5	37.4
MD5030ZBUK	2208	150	30.0	30.0	32.4
MD5030ZBUL	2171	150	30.0	34.5	32.4
MD5030ZBUM	2356	150	30.0	30.0	35.4
MD5030ZBUN	2312	150	30.0	34.5	35.4
MD5030ZBVK	2360	150	30.0	30.0	34.4
MD5030ZBVL	2326	150	30.0	34.5	34.4
MD5030ZBVM	2503	150	30.0	30.0	37.4
MD5030ZBVN	2463	150	30.0	34.5	37.4
MD5030ZBWK	2424	150	30.0	30.0	34.4
MD5030ZBWL	2391	150	30.0	34.5	34.4
MD5030ZBWM	2566	150	30.0	30.0	37.4
MD5030ZBWN	2527	150	30.0	34.5	37.4
MD5030ZLHK	2446	150	30.0	30.0	32.4
MD5030ZLHL	2416	150	30.0	34.5	32.4
MD5030ZLHM	2508	150	30.0	30.0	35.4
MD5030ZLHN	2477	150	30.0	34.5	35.4
MD5030ZLJK	2483	150	30.0	30.0	33.4
MD5030ZLJL	2455	150	30.0	34.5	33.4
MD5030ZLJM	2543	150	30.0	30.0	36.4
MD5030ZLJN	2513	150	30.0	34.5	36.4
MD5030ZLKK	2294	150	30.0	30.0	32.4
MD5030ZLKL	2267	150	30.0	34.5	32.4
MD5030ZLKM	2347	150	30.0	30.0	35.4
MD5030ZLKN	2319	150	30.0	34.5	35.4



MD5030ZLLK	2340	150	30.0	30.0	33.4
MD5030ZLLL	2314	150	30.0	34.5	33.4
MD5030ZLLM	2391	150	30.0	30.0	36.4
MD5030ZLLN	2364	150	30.0	34.5	36.4
MD5030ZLMK	2361	150	30.0	30.0	34.4
MD5030ZLML	2337	150	30.0	34.5	34.4
MD5030ZLMM	2411	150	30.0	30.0	37.4
MD5030ZLMN	2385	150	30.0	34.5	37.4
MD5030ZLUK	2206	150	30.0	30.0	32.4
MD5030ZLUL	2165	150	30.0	34.5	32.4
MD5030ZLUM	2284	150	30.0	30.0	35.4
MD5030ZLUN	2240	150	30.0	34.5	35.4
MD5030ZLVK	2346	150	30.0	30.0	34.4
MD5030ZLVL	2308	150	30.0	34.5	34.4
MD5030ZLVM	2422	150	30.0	30.0	37.4
MD5030ZLVN	2381	150	30.0	34.5	37.4
MD5030ZLWK	2405	150	30.0	30.0	34.4
MD5030ZLWL	2367	150	30.0	34.5	34.4
MD5030ZLWM	2480	150	30.0	30.0	37.4
MD5030ZLWN	2440	150	30.0	34.5	37.4