




SERIES 200 STEEL DOUBLE-FLOW PARTS LIST



Ref. No.	DESCRIPTION OF PARTS	MODELS — QUANTITIES USED												
		211-111	211-121	211-211	211-221	211-311	212-411	212-421	212-511	212-521	212-611	212-621	212-711	212-721
1	MOTOR													
	5 H.P., 1800 RPM, PROTECTED, 184T	1												
	7½ H.P., 1800 RPM, PROTECTED, 213T		1	1										
	15 H.P., 1800 RPM, PROTECTED, 254T				1	1	1							
	20 H.P., 1800 RPM, PROTECTED, 256T							1	1					
	25 H.P., 1800 RPM, PROTECTED, 284T									1	1			
	40 H.P., 1800 RPM, PROTECTED, 324T											1	1	
	50 H.P., 1800 RPM, PROTECTED, 326T													1
2	GEAREDUCER													
	SERIES 10T, 2.615/1 RATIO		1											
	SERIES 10T, 3.27/1 RATIO	1		1										
	SERIES 20T, 2.71/1 RATIO				1									
	SERIES 20T, 3.27/1 RATIO							1						
	SERIES 20T, 3.78/1 RATIO					1	1		1	1	1			
	SERIES 22.2, 3.45/1 RATIO											1		
SERIES 22.2, 4.10/1 RATIO												1	1	
3	FAN													
	60" DIA. H-3-6	1	1											
	72" DIA. H-3-6			1	1									
	84" DIA. H-3-6					1	1	1						
	96" DIA. H-3-8								1	1	1	1		
108" DIA. H-3-9												1	1	
4	DRIVE SHAFT													
	TYPE Q1, 1'-9¼" OVERALL	1	1											
	TYPE Q1, 2'-3¼" OVERALL			1										
	TYPE 6Q, 1'-10½" OVERALL				1									
	TYPE 6Q 2'-4½" OVERALL					1	1	1						
	TYPE 6Q 2'-10½" OVERALL								1					
	TYPE 6Q 2'-9½" OVERALL									1	1			
	TYPE 6Q, 2'-7½" OVERALL											1		
TYPE 6Q, 3'-1½" OVERALL												1	1	
5	FLOAT VALVE — 1¼" or 2½" DIA. MARLEY	SIZE VARIES WITH DESIGN GPM												