


**PERMATOWER II
 SERIES 51000 WOOD DOUBLE-FLOW PARTS LIST
 for
 MODELS 51103, 51105, 51107, 51109, 51111, 51113, 51115, 51117, 51119, 51121, 51123**



Ref. No.	DESCRIPTION OF PARTS	MODELS — QUANTITIES USED											
		51103	51105	51107	51109	51111	51113	51115	51117	51119	51121	51123	
1	MOTOR												
	5 H.P., 1800 RPM, PROTECTED	1											
	7.5 H.P., 1800 RPM, PROTECTED		1	1									
	10 H.P., 1800 RPM, PROTECTED				1	1							
	15 H.P., 1800 RPM, PROTECTED						1	1					
	20 H.P., 1800 RPM, PROTECTED								1	1	1		
25 H.P. 1800 RPM, PROTECTED												1	
2	GEAREDCER												
	SERIES 10T, 2.615/1 RATIO	1	1										
	SERIES 20T, 3.27/1 RATIO			1	1								
	SERIES 20T, 4.11/1 RATIO					1	1			1	1	1	
SERIES 20T, 3.78/1 RATIO							1	1					
3	FAN												
	60" DIA. H-3-6	1	1										
	72" DIA. H-3-6			1	1								
	84" DIA. H-3-6					1	1						
	84" DIA. H-3-8							1	1				
96" DIA. H-3-10									1	1	1		
4	DRIVE SHAFT												
	TYPE Q1 1'-9-1/4" OVERALL	1	1										
	TYPE 6Q 1'-11-1/2" OVERALL			1	1								
	TYPE 6Q 2'-5-1/2" OVERALL					1							
	TYPE 6Q 2'-4-1/2" OVERALL						1	1	1				
TYPE 6Q 2'-10-1/2" OVERALL									1	1	1		
5	FLOAT VALVE — 1-1/4" or 2-1/2" DIA. MARLEY												
		SIZE VARIES WITH DESIGN GPM											