




SERIES NC STEEL DOUBLE-FLOW PARTS LIST
for
MODELS 8904, 8905, 8906, 8907, 8908, 8910, 8911, 8912, 8913, 8914, 8915, 8916, 8917 and 8918



Ref. No.	DESCRIPTION OF PARTS	MODELS — QUANTITIES USED													
		8904	8905	8906	8907	8908	8910	8911	8912	8913	8914	8915	8916	8917	8918
1	MOTOR														
	5 H.P., 1800 RPM, PROTECTED, 184T	1													
	7½ H.P., 1800 RPM, PROTECTED, 213T		1		1										
	10 H.P., 1800 RPM, PROTECTED, 215T			1											
	15 H.P., 1800 RPM, PROTECTED, 254T					1	1	1							
	20 H.P., 1800 RPM, PROTECTED, 256T								1	1					
	25 H.P., 1800 RPM, PROTECTED, 284T										1	1			
	40 H.P., 1800 RPM, PROTECTED, 324T												1	1	
50 H.P., 1800 RPM, PROTECTED, 326T														1	
2	GEAREDUCER														
	SERIES 10T, 2.615/1 RATIO		1												
	SERIES 10T, 3.27/1 RATIO	1			1										
	SERIES 20T, 2.71/1 RATIO			1	1										
	SERIES 20T, 3.27/1 RATIO								1						
	SERIES 20T, 3.78/1 RATIO						1	1		1	1	1			
	SERIES 22.2, 3.45/1 RATIO												1		
SERIES 22.2, 4.10/1 RATIO													1	1	
3	FAN														
	60" DIA. H-3-6	1	1	1											
	72" DIA. H-3-6				1	1									
	84" DIA. H-3-6						1	1	1						
	96" DIA. H-3-8									1	1	1	1		
	108" DIA. H-3-9													1	1
4	DRIVE SHAFT														
	TYPE Q1, 1'-9¼" OVERALL	1	1												
	TYPE 6Q, 1'-4½" OVERALL			1											
	TYPE Q1, 2'-3¼" OVERALL				1										
	TYPE 6Q, 1'-10½" OVERALL					1									
	TYPE 6Q, 2'-4½" OVERALL						1	1	1						
	TYPE 6Q, 2'-10½" OVERALL									1					
	TYPE 6Q, 2'-9½" OVERALL										1	1			
	TYPE 6Q, 2'-7½" OVERALL												1		
	TYPE 6Q, 3'-1½" OVERALL													1	1
5	FLOAT VALVE — 1¼" or 2½" DIA. MARLEY	SIZE VARIES WITH DESIGN GPM													