

Overall values are A-weighted (dBA)
Sound Pressure Level (SPL) expressed in dB (re: 20x10-6 Pa)
Sound Power Level (PWL) expressed in dB (re: 1x10-12 watts)
*Calculated value per CTI ATC-128 test code 2025 revision

Product Name	Sound Pressure Level - Corresponding face and distance from unit										Sound Power Level*
NX	End 1		Side 1		End 2		Side 2		Overhead		
	1.5m	15m	1.5m	15m	1.5m	15m	1.5m	15m	1.5m	15m	
Model											PWL
NX1010KAN#	66	56	72	60	66	56	72	60	72	64	96
NX1010MAN#	69	57	75	64	69	57	75	64	75	67	99
NX1010NAN#	69	63	77	63	69	63	77	63	77	68	100
NX1010PAN#	71	62	77	67	71	62	77	67	79	71	103
NX1015KAN#	61	55	66	57	61	55	66	57	66	58	90
NX1015MAN#	62	56	69	59	62	56	69	59	69	60	92
NX1015NAN#	68	55	72	62	68	55	72	62	72	64	96
NX1015PAN#	69	62	74	65	69	62	74	65	76	68	100
NX1020NAN#	62	54	68	59	62	54	68	59	71	64	95
NX1020PAN#	65	58	72	62	65	58	72	62	75	67	99
NX1020QAN#	70	60	76	69	70	60	76	69	79	71	103
NX1025NAN#	63	53	71	59	63	53	71	59	73	64	95
NX1025PAN#	65	56	72	60	65	56	72	60	74	66	98
NX1025QAN#	70	60	75	65	70	60	75	65	78	70	102
NX2030PLN#	64	56	73	58	64	56	73	58	76	63	95
NX2030QLN#	66	58	75	60	66	58	75	60	78	65	97
NX2030RLN#	68	60	76	61	68	60	76	61	80	66	98
NX2030SLN#	69	61	78	62	69	61	78	62	82	68	99
NX2040PLN#	64	56	74	62	64	56	74	62	78	67	99
NX2040QLN#	66	59	77	64	66	59	77	64	81	69	101
NX2040RLN#	67	59	78	65	67	59	78	65	82	71	103
NX2040SLN#	68	60	79	66	68	60	79	66	83	72	104
NX2050QLN#	64	56	73	63	64	56	73	63	77	68	100
NX2050RLN#	65	58	75	65	65	58	75	65	79	70	102
NX2050SLN#	65	58	75	65	65	58	75	65	79	70	102
NX2060QLN#	63	56	72	63	63	56	72	63	77	68	100
NX2060RLN#	64	57	73	63	64	57	73	63	78	69	100
NX2060SLN#	65	58	74	64	65	58	74	64	79	69	101
NX2060TLN#	67	60	77	67	67	60	77	67	82	72	104
NX2030PCN#	60	52	68	55	60	52	68	55	68	58	90
NX2030QCN#	61	54	70	56	61	54	70	56	70	59	91
NX2030RCN#	63	55	71	58	63	55	71	58	71	61	93
NX2030SCN#	63	55	73	59	63	55	73	59	74	62	94
NX2040PCN#	59	51	68	55	59	51	68	55	65	61	93
NX2040QCN#	61	54	70	57	61	54	70	57	69	60	92
NX2040RCN#	63	55	71	58	63	55	71	58	71	61	93
NX2040SCN#	64	56	72	60	64	56	72	60	72	62	94
NX2050QCN#	59	52	64	55	59	52	64	55	64	58	90
NX2050RCN#	59	53	65	56	59	53	65	56	65	58	90
NX2050SCN#	60	53	66	57	60	53	66	57	66	59	91
NX2060QCN#	60	53	64	56	60	53	64	56	65	58	91
NX2060RCN#	57	51	64	56	57	51	64	56	65	58	90
NX2060SCN#	59	51	64	56	59	51	64	56	66	58	91
NX2060TCN#	60	53	66	57	60	53	66	57	68	59	92