

Capacity Represented in Water Flow (gpm)
 [1] Water flow above maximum allowed for this model, maximum shown
 [2] Performance information not available for these conditions

Input
 Output

ProductName	Conditions	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48	49				
NX	HotWater	67	70	72	72	77	72	75	77	77	82	77	80	82	82	87	82	85	87	87	92	87	90	92	92	97	92	95	97	97	102	97	100	102	102	107	102	105	107	107	112	107	110	112	112	117	89.6	95	98.6	98.6				
	ColdWater	57	60	62	57	62	62	65	67	62	67	67	70	72	67	72	72	75	77	77	72	77	77	80	82	82	85	87	82	87	82	87	87	90	92	92	95	97	92	95	97	92	97	100	102	97	100	102	97	102	80.6	85	89.6	89.6
	WetBulb	50	50	50	50	50	55	55	55	55	55	60	60	60	60	60	65	65	65	65	65	65	70	70	70	70	70	75	75	75	75	75	80	80	80	80	80	85	85	85	85	85	85	90	90	90	90	90	90	90	69.8	78	80.6	82.4
NX1010KAN	Output	192	255	300	[2]	227	212	283	333	167	252	236	315	371	185	281	263	352	414	207	314	294	394	463	231	352	330	442	518	259	395	371	496	580	291	444	418	556	[2]	328	499	470	622	[2]	370	560	452	354	494	430				
	NX1010MAN	217	291	342	170	258	241	323	380	188	287	268	360	424	210	320	300	403	474	234	359	336	451	530	263	402	377	506	594	295	452	425	568	639[1]	333	508	478	636	[2]	375	571	539	639[1]	[2]	423	639[1]	518	405	566	492				
	NX1010NAN	240	322	380	187	286	266	358	423	208	318	297	400	471	232	355	332	447	527	259	398	373	501	589	291	447	419	562	639[1]	327	503	472	630	639[1]	369	565	531	639[1]	[2]	417	634	598	639[1]	[2]	470	639[1]	575	450	628	547				
	NX1010PAN	263	354	418	204	313	292	394	465	227	349	326	440	518	254	391	365	492	579	284	438	410	552	639[1]	319	492	461	618	639[1]	360	553	519	639[1]	639[1]	406	621	585	639[1]	[2]	458	639[1]	639[1]	[2]	518	639[1]	633	495	639[1]	602					
	NX1015KAN	295	391	459	[2]	348	326	433	508	[2]	386	362	482	565	285	430	403	537	629	318	480	450	600	702	355	537	504	671	783	397	601	565	750	871	446	674	635	837	[2]	501	754	712	916[1]	[2]	564	843	686	540	748	653				
	NX1015MAN	326	434	509	[2]	385	360	481	564	283	428	401	535	628	314	477	447	597	700	351	533	500	667	780	393	596	560	745	870	440	668	628	833	916[1]	495	749	706	916[1]	[2]	557	838	792	916[1]	[2]	627	916[1]	763	600	831	726				
	NX1015NAN	356	476	559	277	422	394	528	621	308	469	439	588	691	343	524	490	656	770	384	586	549	734	858	430	656	616	820	916[1]	483	735	691	916[1]	916[1]	543	824	777	916[1]	[2]	612	916[1]	871	916[1]	[2]	689	916[1]	839	660	914	799				
	NX1015PAN	399	535	630	310	474	443	595	700	345	528	494	663	778	385	590	552	740	867	431	660	618	827	916[1]	484	739	694	916[1]	916[1]	544	829	779	916[1]	916[1]	612	916[1]	875	916[1]	[2]	690	916[1]	916[1]	[2]	777	916[1]	816[1]	744	916[1]	899					
	NX1020NAN	402	534	625	315	475	[3]	591	692	349	527	494	656	767	388	586	550	730	852	433	654	614	814	947	484	730	687	907	1050	542	816	769	1009	1101[1]	609	911	860	1101[1]	[2]	683	1015	961	[2]	[2]	767	1101[1]	926	735	1006	884				
	NX1020PAN	464	619	726	361	550	[3]	686	804	402	611	572	763	893	448	681	638	850	991	500	760	714	947	1100	561	850	799	1054	1101[1]	629	949	894	1101[1]	1101[1]	707	1059	1001	1101[1]	[2]	795	1101[1]	1101[1]	[2]	[2]	893	1101[1]	1076	855	1101[1]	1028				
	NX1020QAN	505	675	791	393	599	[3]	748	876	437	666	623	831	970	487	742	696	924	1075	545	828	778	1028	1101[1]	611	924	870	1101[1]	1101[1]	686	1031	972	1101[1]	1101[1]	771	1101[1]	1085	1101[1]	[2]	865	1101[1]	1101[1]	[2]	[2]	970	1101[1]	1101[1]	930	1101[1]	1101[1]				
	NX1025NAN	482	641	751	378	570	[3]	710	832	419	632	592	789	925	466	704	660	879	1030	519	786	738	982	1147	581	879	826	1097	1276	651	985	927	1224	1392[1]	731	1102	1039	1363	[2]	822	1232	1165	[2]	[2]	925	1373	1121	885	1220	1068				
	NX1025PAN	530	707	828	414	628	[3]	783	917	460	697	653	870	1018	512	777	728	969	1131	572	867	814	1080	1257	640	969	911	1203	1392[1]	718	1083	1020	1339	1392[1]	806	1209	1142	1392[1]	[2]	906	1347	1276	[2]	[2]	1018	1392[1]	1229	975	1335	1173				
	NX1025QAN	591	791	929	461	702	[3]	878	1030	512	781	730	976	1144	571	871	816	1088	1271	639	973	913	1213	1392[1]	716	1088	1023	1352	1392[1]	804	1217	1146	1392[1]	1392[1]	904	1359	1283	1392[1]	[2]	1017	1392[1]	1392[1]	[2]	[2]	1144	1392[1]	1381	1095	1392[1]	1318				
	NX2030PLN	[2]	[2]	906	[2]	[2]	[2]	856	1006	[2]	[2]	[2]	954	1120	[2]	854	[2]	1065	1249	[2]	955	892	1190	1393	[2]	1068	1000	1330	1555	[2]	1195	1121	1487	1733	884	1337	1258	1662	1832[1]	993	1496	1411	1832[1]	1832[1]	1116	1671	1360	1071	1482	1294				
	NX2030QLN	[2]	[2]	994	[2]	[2]	[2]	939	1105	[2]	[2]	[2]	1047	1231	[2]	937	874	1170	1373	[2]	1048	979	1307	1532	[2]	1173	1098	1462	1709	863	1313	1232	1635	1832[1]	970	1470	1382	1826	1832[1]	1091	1644	1551	1832[1]	1832[1]	1227	1832[1]	1496	1176	1630	1422				
	NX2030RLN	[2]	899	1059	[2]	[2]	[2]	1000	1177	[2]	893	[2]	1115	1311	[2]	998	930	1246	1462	[2]	1116	1042	1393	1632	[2]	1250	1169	1558	1821	918	1399	1312	1742	1832[1]	1033	1566	1473	1832[1]	1832[1]	1162	1752	1652	1832[1]	1832[1]	1307	1832[1]	1594	1253	1736	1515				
	NX2030SLN	[2]	947	1115	[2]	[2]	[2]	1054	1240	[2]	941	875	1175	1382	[2]	1051	980	1313	1542	[2]	1176	1098	1469	1721	860	1317	1232	1643	1832[1]	967	1475	1384	1832[1]	1832[1]	1088	1652	1553	1832[1]	1832[1]	1224	1832[1]	1743	1832[1]	1832[1]	1378	1832[1]	1681	1321	1831	1598				
	NX2040PLN	[2]	978	1144	[2]	876	[2]	1084	1267	[2]	973	908	1204	1405	[2]	1082	1012	1338	1559	[2]	1205	1130	1490	1732	895	1342	1262	1658	1924	1002	1496	1409	1846	2135	1122	1666	1574	2053	2157[1]	1256	1855	1758	2157[1]	[2]	1406	2063	1694	1348	1841	1617				
	NX2040QLN	[2]	1074	1257	[2]	962	895	1191	1392	[2]	1068	996	1323	1545	[2]	1189	1111	1471	1715	878	1324	1241	1638	1906	983	1476	1387	1824	2116	1101	1645	1550	2030	2157[1]	1233	1833	1732	2157[1]	2157[1]	1381	2041	1934	2157[1]	[2]	1546	2157[1]	1863	1482	2025	1779				
	NX2040RLN	858	1144	1340	[2]	1024	953	1269	1485	[2]	1138	1061	1410	1647	[2]	1267	1184	1569	1830	935	1412	1323	1747	2033	1047	1574	1478	1946	2157[1]	1173	1755	1653	2157[1]	2157[1]	1314	1955	1847	2157[1]	2157[1]	1472	2157[1]	2062	2157[1]	[2]	1649	2157[1]	1988	1581	2157[1]	1897				
	NX2040SLN	904	1206	1413	[2]	1079	1004	1337	1565	[2]	1200	1118	1487	1737	880	1335	1248	1655	1930	985	1488	1394	1843	2143	1103	1660	1559	2052	2157[1]	1236	1851	1743	2157[1]	2157[1]	1385	2062	1948	2157[1]	2157[1]	1552	2157[1]	2157[1]	2157[1]	[2]	1739	2157[1]	2096	1667	2157[1]	2001				
	NX2050QLN	967	1271	1477	[2]	1143	1068	1402	1630	[2]	1264	1184	1552	1801	943	1400	1315	1720	1992	1050	1554	1462	1908	2203	1170	1725	1628	2115	2431	1305	1916	1813	2342	[2]	1457	2126	2018	[2]	[2]	1626	2355	2243	[2]	[2]	1814	[2]	2157	1736	2336	2068				
	NX2050RLN	1030	1354	1575	[2]	1218	1139	1495	1738	[2]	1347	1262	1655	1921	1005	1492	1401	1835	2125	1119	1657	1559	2035	2349	1247	1840	1736	2256	2479[1]	1391	2044	1933	2479[1]	[2]	1553	2267	2152	[2]	[2]	1734	2479[1]	2391	[2]	[2]	1935	[2]	2300	1852	2479[1]	2206				
	NX2050SLN	1085	1426	1659	[2]	1282	1199	1575	1831	952	1418	1328	1743	2025	1059	1572	1476	1934	2240	1179	1745	1642	2145	2475	1313	1939	1829	2378	2479[1]	1465	2154																							