

MARLEY SERIES 4800 AQUATOWER®

SERVICE PARTS - 60 CYCLE MOTOR APPLICATIONS

PL-4800C

Use this table to help you order repair and replacement parts for your Series 4800 Aquatower. The numbers in the table are Marley part numbers which will expedite processing your order. Contact your local Marley Application Engineer for prices and availability; to place your order; or for help with identifying the parts you need.

Tower Model		4811	4812	4821	4822	4831	4832	4841	4842	4851	4852	4853	4861	4862	4871	4872
V-Belts	A75	693531L	693531L													
	A100			609347L												
	A105				320333L											
	A112					221820L	221820L	221820L	221820L							
	2 - A120									216218L	216218L	216218L				
	B140												617407L			
	2 - B144													216556L	216556L	216556L
Motor Sheaves†		082172L	094979L	082859L	106310L	082859L	112292L	095778L	107508L	571562L	180398L	211136L	112169L	217497L	212100L	215822L
Fan Sheaves		135210L	135210L	135210L	135210L	154856L	154856L	154245L	154245L	427179L	427179L	427179L	427286L	427286L	427286L	427286L
Fans	24" Diameter Revcor KH 2404-38	436741M	436741M	436741M	436741M											
	36" Diameter Revcor KH 3604-36					437046M	437046M									
	42" Diameter Revcor KH 4204-30							437582M	437582M							
	48" Diameter Revcor KH 4804-30									439109M	439109M	439109M				
	54" Diameter Air Turbine Y-54-11												024869M	024869M		
	66" Diameter Air Turbine Y-66-11														338129L	338129L
Bearing Assemblies	Marley Series 1300SE	B60764M	B60764M	B60764M	B60764M	B60764M	B60764M	B60764M	B60764M							
	Marley Series 118SE									574194M	574194M	574194M	574194M	574194M	574194M	574194M
Fan Guards	24" Diameter HDG	B43152L	B43152L	B43152L	B43152L											
	36" Diameter HDG					B28868L	B28868L									
	42" Diameter HDG							B28869L	B28869L							
	48" Diameter HDG									B28870L	B28870L	B28870L				
	54" Diameter HDG												B28871L	B28871L		
	66" Diameter HDG														B28872L	B28872L
Float Valves	Brass Body 3/4" NPT	155929M	155929M	155929M	155929M	155929M	155929M	155929M	155929M	155929M	155929M	155929M	155929M	155929M	155929M	155929M
	Brass Stem	720755M	720755M	720755M	720755M	720755M	720755M	720755M	720755M	088708M	088708M	088708M	088708M	088708M	088708M	088708M
	Plastic Float	720680M	720680M	720680M	720680M	720680M	720680M	720680M	720680M	720680M	720680M	720680M	720680M	720680M	720680M	720680M
Distribution Nozzles – Quantity		10	10	14	14	14	14	22	22	44	44	44	60	60	76	76

† Motor sheave part number shown is for standard motor frames only. Since your sheave may be different, please have your tower serial number available when you order these parts.

Note: All quantities are one (1) per tower, except nozzles. Nozzle quantities vary as shown.

See reverse side for motors.

MARLEY SERIES 4800 AQUATOWER

REPLACEMENT MOTORS - 60 CYCLE MOTOR APPLICATIONS

Tower Model	4811	4812	4821	4822	4831	4832	4841	4842	4851	4852	4853	4861	4862	4871	4872
1/3 HP 1/60/115/230/1800 RPM 56 Frame*	454215L*														
3/4 HP 1/60/115/230/1800 RPM 56 Frame		200113L	200113L	200113L	200113L										
1 HP 3/60/200/1800 RPM 143T Frame		C04703L	C04703L	C04703L	C04703L										
1 HP 3/60/230/460/1800 RPM 143T Frame*		C04704L*	C04704L*	C04704L*	C04704L*										
1 HP 3/60/575/1800 RPM 143T Frame		C04705D	C04705D	C04705D	C04705D										
2 HP 3/60/200/1800 RPM 145T Frame						C04719L	C04719L		C04719L						
2 HP 3/60/230/460/1800 RPM 145T Frame*						C04720L*	C04720L*		C04720L*						
2 HP 3/60/575/1800 RPM 145T Frame						C04721L	C04721L		C04721L						
3 HP 3/60/200/1800 RPM 182T Frame								C04736L		C04736L					
3 HP 3/60/230/460/1800 RPM 182T Frame*								C04737L*		C04737L*					
3 HP 3/60/575/1800 RPM 182T Frame								C04738D		C04738D					
5 HP 3/60/200/1800 RPM 184T Frame											C11602L	C11602L			
5 HP 3/60/230/460/1800 RPM 184T Frame*											C11604L	C11604L			
5 HP 3/60/575/1800 RPM 184T Frame											C11606D	C11606D			
7-1/2 HP 3/60/200/1800 RPM 213T Frame													C11618L	C11618L	
7-1/2 HP 3/60/230/460/1800 RPM 213T Frame*													C11620L*	C11620L*	
7-1/2 HP 3/60/575/1800 RPM 213T Frame													C11622D	C11622D	
7-1/2 HP 3/60/208/1800/900 RPM 215T Frame													235085D	235085D	
7-1/2 HP 3/60/460/1800/900 RPM 215T Frame													652636L	652636L	
7-1/2 HP 3/60/575/1800/900 RPM 215T Frame													235168D	235168D	
10 HP 3/60/200/1800 RPM 215T Frame															C04706L
10 HP 3/60/230/460/1800 RPM 215T Frame*															C04708L*
10 HP 3/60/575/1800 RPM 215T Frame															C04711L
10 HP 3/60/200/1800/900 RPM 254T Frame															119594D
10 HP 3/60/460/1800/900 RPM 254T Frame															198754L
10 HP 3/60/575/1800/900 RPM 254T Frame															246371D

* Indicates standard motor for each model. Other motors shown are supplied for particular electrical supply characteristics.
Check your motor's nameplate before you order to make sure you select the correct motor for your installation.



Marley Cooling Tower

A United Dominion Company

The Marley Cooling Tower Company
7401 West 129 Street • Overland Park, Kansas 66213
Tel (913) 664-7400