



4600 SERIES AQUATOWER PARTS LIST

**Models 4613, 4615, 4617, 4619, 4621, 4623, 4625, 4627, 4629, 4631 & 4633
(SEE ITEMIZED PARTS LIST ON REVERSE SIDE)**



Models
4613 through 4633



Mechanical Equipment

IMPORTANT – The serial and model numbers of tower must be provided when ordering parts.

AQUATOWER PARTS LIST***

REF.	DESCRIPTION OF PARTS	MODEL QUANTITIES												
		4613	4615	4617	4619	4621	4623	4625	4627	4629	4631	4633		
1	MOTOR*													
	1/3 H.P., 1750 RPM, TENV.	1	1	1										
	1/2 H.P., 1750 RPM, TEFC.				1	1								
	3/4 H.P., 1750 RPM, TEFC.						1							
	1 H.P., 1750 RPM, PROT.							1	1					
	1-1/2 H.P., 1750 RPM, PROT.										1			
	2 H.P., 1750 RPM, PROT.											1		
	3 H.P., 1750 RPM, PROT.												1	
2	MOTOR SHEAVE													
	KEYWAY													
	Browning, AK 49 5/8" Bore 3/16 x 3/32						1							
	Browning, AK 51 5/8" Bore 3/16 x 3/32				1									
	Browning, AK 54 5/8" Bore 3/16 x 3/32		1											
	Browning, AK 59 5/8" Bore 3/16 x 3/32			1										
	Browning, AK 46 5/8" Bore 3/16 x 3/32	1				1								
	Browning, AK 51 7/8" Bore 3/16 x 3/32							1						
	Browning, ITB 50 with "PI" Bushing 7/8" Bore 3/16 x 3/32								1					
	Browning, ITA 46 with "PI" Bushing 7/8" Bore 3/16 x 3/32										1			
	Browning, AK 56 7/8" Bore 3/16 x 3/32											1		
Browning, ITB 52 with "PI" Bushing 1-1/8" Bore 1/4 x 1/8												1		
3	FAN SHEAVE													
	Browning, AK 99 3/4" Bore 3/16 x 3/32	1			1									
	Browning, AK 134 3/4" Bore 3/16 x 3/32		1					1						
	Browning, AK 144 3/4" Bore 3/16 x 3/32			1			1				1			
	Browning, AK 154 3/4" Bore 3/16 x 3/32					1								
	Browning, AK 184 3/4" Bore 3/16 x 3/32											1		
	Browning, BK 190 3/4" Bore 3/16 x 3/32								1					
	Browning, BK 160 3/4" Bore 3/16 x 3/32													1
4	V-BELT													
	Browning, A 68	1												
	Browning, A 87		1											
	Browning, B 133								1					
	Browning, A 110			1	1			1						
	Browning, A 112					1	1							
	Browning, A 128											1	1	
	Browning, A 120										1			
Browning, B 124														
5	FAN** TORRINGTON													
	24" Dia., N2424-4 3/4" Bore 3/16 x 3/32	1												
	24" Dia., N2436-4 3/4" Bore 3/16 x 3/32		1	1	1									
	36" Dia., R3627-4 with "H" Bushing 3/4" Bore 3/16 x 3/32					1	1	1						
	42" Dia., R4227-4 with "H" Bushing 3/4" Bore 3/16 x 3/32								1	1				
48" Dia., R4827-4 with "H" Bushing 3/4" Bore 3/16 x 3/32											1	1		
6	BEARING HOUSING													
	Including shaft and bearings 6-3494-2	1	1	1	1	1	1	1	1	1	1	1	1	1
	Bearings only (2 required) 52-155													
Oil seals only (2 required) SS-5166														
7	FLOAT VALVE ASSEMBLY													
	3/4" Flippen with ball and rod	1	1	1	1	1	1	1	1	1	1	1	1	1

*1/3 H.P. Motor Available in Single Phase Only.

1/2 H.P., 3/4 H.P. and 1 H.P. Motors Available in Single Phase or 3 Phase.

1-1/2 H.P., 2 H.P., and 3 H.P. Motors Available in 3 Phase Only.

When Ordering Replacement Motor, Specify Voltage and Phase Required.

**24" Dia. Fans Have Hub on Inlet Side. All Other Fans Have Hub on Exhaust Side.

***This Parts List Effective for the 4600 Aquatowers Starting with the Following Serial Numbers:

4613 - 601	4621 - 491	4629 - 526
4615 - 631	4623 - 426	4631 - 406
4617 - 697	4625 - 506	4633 - 1155
4619 - 871	4627 - 526	