



LLC Control Panel Features:

- NEMA 4X Fiberglass Enclosure
- Mounting flanges located top and bottom
- Outdoor rated
- Stainless steel continuous hinge
- Swing out lid with stainless steel clamps
- Lock-off capabilities
- 14" high x 12" wide enclosure for configurations up to 4 cards
- 18" high x 16" wide enclosure for configurations up to 6 cards

Electrical Components:

- Main breaker disconnect
- HAND-OFF-AUTO selector switch for manual fill control when makeup card is used
- Output contact for makeup card is internally powered with 120 VAC for use by customer
- User terminal points for connecting field devices e.g. solenoid, water level probes and alarm devices
- Terminal strip raised for easy access
- Wiring diagram and User Manual secured in literature pocket inside the panel door
- Built to UL and CUL standards
- Single enclosure for all control cards
- Level cards as required for following conditions:
 - Make up
 - Hi alarm
 - Lo alarm
 - Hi level cutout
 - Lo level cut out



SPX

COOLING TECHNOLOGIES

7401 WEST 129 STREET | OVERLAND PARK, KANSAS 66213 UNITED STATES | 913 664 7400 | spxcooling@spx.com | spxcooling.com

In the interest of technological progress, all products are subject to design and/or material change without notice.
©2009 SPX Cooling Technologies, Inc. | Printed in USA

SPEC-LLC-09