



CoolBoost Fan and Pump Control Panel Features

- NEMA 4X Fiberglass Enclosure
- Hinged and lockable outer door
- Swing-out dead-front inner door
- Outdoor rated

Electrical Components

- External disconnect handle with padlocking provision to meet lockout, tag-out safety requirements
- Main circuit breaker with thermal and magnetic overload protection
- Solid-state temperature controller with two-line display showing set point temperature and coil fluid temperature
- Door mounted operators
- Fan and pump starters
- Pilot lights
- Status contacts
- Marley RTD with dry well and 1/2" NPT pipe connection
- Wiring diagram laminated and mounted on inside
- Built to UL508 and CUL508 safety requirements

Options

- Single point power connection concept for electrical contractors power feed
- Integrated basin heater controls
- Integrated water level controls
- Integrated damper circuit
- Integrated VFD feeder breaker for remote VFD
- Factory installed and wired on selected fluid cooler models

