

Capacity Represented in Flow (gpm)
N/A: Capacity outside hydraulic limits for this model.

Product Name	Additive Type	Additive Content (%)
--------------	---------------	----------------------

Hot Water
Cold Water
West Bubb

Base Model	Coil	HP	Pump HP
------------	------	----	---------

67	70	72	77	75	72	75	77	82	80	77	80	82	87	85	82	85	87	92	90	87	90	92	97	95	92	95	97	102	100	97	100	102	107	105	102	105	107	112	110	107	110	112	117	115	89.6	102	98.6	98.6	95
----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	-----	-----	----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	------	-----	------	------	----

Flow #1 Inlet Connections	Flow #1 Inlet (Qty)-Size	Flow #1 Inlet (PSI @ 30°F)	Flow #2 Inlet Connections	Flow #2 Inlet (Qty)-Size	Flow #2 Inlet (PSI @ 30°F)	Flow #3 Inlet Connections	Flow #3 Inlet (Qty)-Size	Flow #3 Inlet (PSI @ 30°F)
---------------------------	--------------------------	----------------------------	---------------------------	--------------------------	----------------------------	---------------------------	--------------------------	----------------------------

Capacity Represented in Flow (gpm)
N/A: Capacity outside hydraulic limits for this model.

Table with columns: Product Name, Additive Type, Additive Content (%), Base Model, Coil, HP, Pump HP. Lists various flow control valves and their specifications.

Hot Water
Cold Water
West Bubb

Main data table with 40 columns representing flow rates for different configurations. Each row corresponds to a product from the first table, and columns show flow capacity in gpm for various flow conditions.

Summary table with columns: Flow #1 Inlet, Flow #1 PD @, Flow #2 Inlet, Flow #2 PD @, Flow #3 Inlet, Flow #3 PD @. Shows inlet and outlet flow rates for the three flow control valves.

