



Fan and Pump Motor Control Panel Features

- NEMA 4X fiberglass enclosure
- Hinged and lockable outer door
- Swing-out dead-front inner door
- Outdoor rated

Electrical Components

- External disconnect handle with padlocking provision to meet lockout, tag-out safety requirements
- Main circuit breaker with thermal and magnetic overload protection
- Solid-state temperature controller with two-line display showing set point temperature and coil fluid temperature
- Door mounted operators
- Fan and pump motor starters
- Pilot lights
- Status contacts
- Marley RTD with dry well and 1/2" NPT pipe connection
- Wiring diagram laminated and mounted inside panel
- Built to UL508 and CUL508 safety requirements

Options

- Single-point power connection for electrical contractors power feed
- Integrated basin heater controls
- Integrated water level controls
- Integrated damper circuit
- Integrated VFD feeder breaker for remote VFD
- Factory installed and wired on select fluid cooler models

SPX COOLING TECHNOLOGIES, INC.

7401 WEST 129 STREET
OVERLAND PARK, KS 66213 USA
913 664 7400 | spxcooling@spx.com
spxcooling.com

SPEC-FCFAN-PUMP-11 | ISSUED 05/2017
COPYRIGHT © 2017 SPX CORPORATION

In the interest of technological progress, all products are subject to design and/or material change without notice.