


Product Benefits

- Monitors and protects 24/7
- Operates off standard +24VDC loop power
- Interfaces with plant monitoring systems
- Installs quickly and easily
- Provides critical vibration information
- Avoids costly catastrophic failures




Part Number	Model	Cable Length	Measurement Range	Output	Frequency Range	Excitation Voltage	Mounting Thread	Electrical Connector	Certification
2407459	640B12/030BZ	30'-0"	0 to 2 in/sec peak	4-20 mA	180 to 60000 cpm 3Hz to 10 kHz	12 to 30VDC	1/4-28 UNF	Integral Cable	CE
2751122	640B12/060BZ	60'-0"							




Sensor Output mA	Vibration Velocity in/sec peak
4.00	0.00
8.00	0.50
12.00	1.00
15.75	1.47
20.00	2.00

Typical Control System Application Diagram



CoolBoost Opti System Application Diagram



SPX COOLING TECH, LLC

7401 WEST 129 STREET
OVERLAND PARK, KS 66213 USA
913 664 7400 | spxcooling@spx.com
spxcooling.com

SPEC-IMIT-23 | ISSUED 03/2023

©2023 SPX COOLING TECH, LLC | ALL RIGHTS RESERVED

In the interest of technological progress, all products are subject to design and/or material change without notice.

